

Coarse/Fine Movement, 1/4-20 w/ Rotation, Rack & Pinion



#59-322

Stock **#59-322** 3-4 DAYS

⊖ 1 ⊕

£485.35

ADD TO CART

Qty 1+

£485.35

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
Rack and Pinion Block: 50 H x30 W x50 L

Travel (mm):
35 (+23/-12) in Y

Type:
Rack and Pinion Mount

Travel Per Knob Rotation (mm):
25.5 coarse, 3.2 fine

Load Capacity (kg):

2.00
Note: 1/4-20 Stud
Type of Movement: Linear (Y), Rotation
Type of Adjustment: Coarse/Fine Movement
Optical Centerline from Post (mm): 51.00
Mounting Post Hole and Thread: 3/4" Diameter Post 1/4-20 Tapped Hole

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
