

TECHSPEC[®] 30mm Sq, 5kg Load Capacity, 8mm Travel, Metric Dovetail Stage



#16-711: Dovetail Stage, 30mm SQ, English



Stock **#16-714** [CONTACT US](#)

-

1

+

£93.50

ADD TO CART

Qty 1-9
£93.50
Qty 10+
£82.45
Volume Pricing
Request Quote
ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive: Lead Screw
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 30 x 30
Travel (mm): 8
Travel (inches): 0.31
Construction: Matte Black Finish Brass
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 5
Mounting Threads: (1) M6 x 1, (8) M2 x 0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 10
Included Hardware: 4X M2 x 0.4, 8mmL Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View