

TECHSPEC® 40mm Sq, 10kg Load Capacity, 14mm Travel, English Dovetail Stage



#16-712: Dovetail Stage, 40mm SQ, English



Stock **#16-712** 3-4 DAYS

⊖ 1 ⊕ **£114.75**

ADD TO CART

Qty 1-9
£114.75
Qty 10+
£101.32
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive: Lead Screw
Drive Orientation: Center Drive
Type: English
Stage Size (mm): 40 x 40
Travel (mm): 14
Travel (inches): 0.55
Construction: Matte Black Finish Brass
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 10
Mounting Threads: (1) ¼-20, (4) 6-32, (8) 2-56
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 10
Included Hardware: 4X 6-32, 5/16"L Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View