

TECHSPEC®

40mm Sq, 10kg Load Capacity, 14mm Travel, Metric Dovetail Stage



#16-712: Dovetail Stage, 40mm SQ, English



Stock **#16-715** 3-4 DAYS

-

1

+

£114.75

ADD TO CART

Qty 1-9

£114.75

Qty 10+

£101.32

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive: Lead Screw
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 40 x 40
Travel (mm): 14
Travel (inches): 0.55
Construction: Matte Black Finish Brass
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 10
Mounting Threads: (1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 10
Included Hardware: 4X M3 x 0.5, 8mmL Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View