

Red, 4" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock #36-556 3-4 DAYS

-

1

+

£1,712.75

ADD TO CART

Qty 1+

£1,712.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Red

Model Number:
DL225-100625IC

Operating Temperature (°C):
0 to +60

Dimensions (mm):
177 L x 110 W x 113 T

Wavelength (nm): 625.00
Weight (g): 1396.2
Working Distance (mm): 25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Diffuse Axial
Illumination Mode: Constant
Aperture Size: ~4" x4"

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
