

SCHOTT BG67 50mm Sq., 1mm Thick Harsh Environment Colored Glass NIR Cut-Off Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-441** CLEARANCE ☐ In Stock

-

1

+

£112.16

ADD TO CART

Qty 1+
£112.16

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Center Wavelength CWL (nm):
510.00

Density (g/cm³):
2.85

Glass/Filter Number:
[SCHOTT BG67](#)

Length (mm):

50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: NA
Surface Quality: 60-40
Transformation Temperature (°C): 390
Thickness (mm): 1.00 ±0.1
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View