

# SCHOTT BG7, 50mm Sq., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-408** ☐ In Stock

- 1 +

£74.80

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £74.80                        |
| Qty 11+                       |
| £66.30                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Center Wavelength CWL (nm):  
488.00

|                                                    |
|----------------------------------------------------|
| Density (g/cm³):<br>2.61                           |
| Glass/Filter Number:<br><a href="#">SCHOTT BG7</a> |
| Length (mm):<br>50.00                              |
| Coating:<br>Uncoated                               |
| Color:<br>Deep Blue                                |
| Index of Refraction n <sub>d</sub> :<br>1.52       |
| Surface Quality:<br>60-40                          |
| Transformation Temperature (°C):<br>468            |
| Thickness (mm):<br>3.00 ±0.2                       |
| Type:<br>Bandpass Filter                           |
| Wavelength:<br>UV-VIS                              |
| Width (mm):<br>50.00                               |
| Bevel:<br>Protective as needed                     |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |