

SCHOTT GG495, 12.5mm Dia., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-440** 3-4 DAYS

- 1 + **£27.20**

ADD TO CART

Qty 1-10
£27.20
Qty 11+
£23.80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
495.00 ±6

Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT GG495
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 560
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s (nm): 430
Surface Quality: 60-40
Transformation Temperature (°C): 535
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
