


SCHOTT NG4, 0.4 OD, 25mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-724** [CONTACT US](#)

-

1

+

£35.70

ADD TO CART

Qty 1-10

£35.70

Qty 11+

£31.45

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.4 ±0.03 @ 546nm

Glass/Filter Number:
[SCHOTT NG4](#)

Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 483
Thickness (mm): 0.70
Thickness Tolerance (mm): (nominal)
Transmission (%): 39.81 ±2.39% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View
