


SCHOTT OG570, 12.5mm Dia., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-444** 3-4 DAYS

- 1 + **£27.20**

ADD TO CART

Qty 1-10
£27.20

Qty 11+
£23.80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
570.00 ±6

Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG570
Coating: Uncoated
Color: Orange
Passband Limit 1 λ_{p1} (nm): 640
Index of Refraction n_d : 1.51
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s (nm): 500
Surface Quality: 60-40
Transformation Temperature (°C): 510
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
