

# SCHOTT RG630, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-515** ☐ In Stock

-

1

+

£65.88

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £65.88                        |
| Qty 11+                       |
| £64.60                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Cut-On Wavelength (nm):  
630.00 ±6

|                                                      |
|------------------------------------------------------|
| Density (g/cm³):<br>2.65                             |
| Glass/Filter Number:<br><a href="#">SCHOTT RG630</a> |
| Length (mm):<br>50.00                                |
| Coating:<br>Uncoated                                 |
| Color:<br>Red                                        |
| Passband Limit 1 $\lambda_{p1}$ (nm):<br>710         |
| Index of Refraction $n_d$ :<br>1.52                  |
| Spectral Transmittance $t_p$ (%):<br>94              |
| Stopband Limit $\lambda_s$ (nm):<br>540              |
| Surface Quality:<br>60-40                            |
| Transformation Temperature (°C):<br>527              |
| Thickness (mm):<br>2.00 ±0.2                         |
| Type:<br>Longpass Filter                             |
| Wavelength:<br>VIS                                   |
| Width (mm):<br>50.00                                 |
| Dimensional Tolerance (mm):<br>±0.2                  |
| Reflection Factor $P_d$ :<br>0.92                    |
| Bevel:<br>Protective as needed                       |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Exempt</a>                |
| Certificate of Conformance:<br><a href="#">View</a> |