

White, 1" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#36-551** 3-4 DAYS

-

1

+

£555.05

ADD TO CART

Qty 1+

£555.05

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Model Number:
DL225-025VH1IC

Operating Temperature (°C):
0 to +60

Dimensions (mm):
106 L x 33 W x 36 T

Weight (g): 187.89
Working Distance (mm): 25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Diffuse Axial
Illumination Mode: Constant
Aperture Size: ~1.1"x1.1"

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)