

TECHSPEC® C-Mount Kinematic Mount (2-Screw Adjustment)



C, S, and T-Mount Kinematic Mounts

Stock #58-870 3-4 DAYS

-

1

+

£100.30

ADD TO CART

Qty 1-4

£100.30

Qty 5+

£90.27

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Mounting Threads:
#8 or M4

Travel (mm):
No Z-Axis Translation

Type:
Tube Mount

Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4.0
Thermal Stability (μrad): <5
Pointing Accuracy (μrad): 1.3
Adjustment Screw Pitch (mm): 0.25
Thread Type: C-Mount
Number of Adjustment Screws: 2
Aperture Size: 1" x32 TPI
Function: Kinematic (Tip-Tilt)
Compatible Post: M4 x0.7, 8-32

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View