

Green M49 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-437 3-4 DAYS

⊖ 1 ⊕ **£163.20**

ADD TO CART

Qty 1-9

£163.20

Qty 10+

£155.04

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-470, 600-952

Clear Aperture CA (mm):
44.00

Coating:
Hard Coated

Filter Thread:
M49 x 0.75

Color:
Green

Center Wavelength CWL (nm):
525.00

Construction:
Mounted in Black Anodized Ring

Full Width-Half Max FWHM (nm):
80.00

Mount Thickness (mm):
5.2

Mount Thickness Including Threads (mm):
7.0

Outer Diameter (mm):
51.00

Substrate Thickness (mm):
1.3

Type:
Mounted Imaging Filter

Minimum Transmission (%):
≥85

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)
