

Coherent® EnergyMax 1191436 | 12μJ - 20mJ, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#88-423** [CONTACT US](#)

-

1

+

£2,341.75

ADD TO CART

Qty 1+

£2,341.75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
10

Connector:
USB

Model Number:
J-10MB-HE
Coherent Part Number: 1191436

Type:
Meterless

Type of Sensor: Pyroelectric
Length of Cable (m): 3.0
Linearity (%): ±3
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 1064
Noise Equivalent Energy (μJ): <1.2
Maximum Repetition Rate (pps): 1000
Maximum Incident Beam Power (W): 4
Maximum Pulse Width (μs): 17
Wavelength Range (nm): 190 - 12000
Maximum Incident Energy Density: 500mJ/cm² (10ns, 1064nm)
Energy Range: 12μJ - 20mJ

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View