

M77 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-409 3-4 DAYS

⊖ 1 ⊕ **£100.30**

ADD TO CART

Qty 1-9

£100.30

Qty 10+

£95.45

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
73.00

Coating:
Hardcoated

Diameter (mm):
80.00

Extinction Ratio:

up to 3000:1 @ ~600nm (nominal)

Filter Thread:

M77 x 0.75

Surface Quality:

40-20

Type:

Mounted Imaging Filter

Construction:

Black Anodized Aluminum

Wavelength Range (nm):

400 - 700

Mount Thickness Including Threads (mm):

11

Regulatory Compliance

RoHS:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)
