

SCHOTT RG9, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-903** 3-4 DAYS

-

1

+

£23.38

ADD TO CART

Qty 1-10
£23.38
Qty 11+
£22.74
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-On Wavelength (nm):
726.00

Density (g/cm³): 2.58
Full Width-Half Max FWHM (nm): 315.00
Glass/Filter Number: SCHOTT RG9
Coating: Uncoated
Color: Black
Index of Refraction n _d : 1.52
Surface Quality: 80-50
Transformation Temperature (°C): 519
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.38

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View