

SF10 25.4 x 25.4mm Ultrafast Prism



Stock **#89-844**

3-4 DAYS

-

1

+

£170.85

ADD TO CART

Qty 1-5

£170.85

Qty 6+

£151.30

Volume Pricing

[Request Quote](#)



 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Substrate:

SF10

Surface Quality:
40-20

Type: Equilateral Prism
Dimensional Tolerance (mm): +0.0/-0.2
Angle Tolerance (arcmin): ±3
Bevel: <0.25mm x45°
Clear Aperture (%): >80
Apex Angle (°): 60.60
Group Velocity Dispersion (fs²/cm): 1600.00
Surface Flatness (P-V): λ/10
Base Width (mm): 25.40
Base Length (mm): 25.4
Group Velocity Dispersion (fs²/mm): 155 @ 800nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant