

White, High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Coaxial LED Spot Light Illuminator

Stock #11-024 3-4 DAYS

⊖ 1 ⊕ **£522.75**

ADD TO CART

Qty 1+

£522.75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Model Number:
SL162-WHIC

Operating Temperature (°C):
0 to 60

Weight (g):
85.1

LED Lifetime (hours):
50,000

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#66-855](#)
Korea: [#33-773](#)
China: [#66-855](#)

Number of LEDs:
1

Length of Cable (m):
2

Type of Illumination:
LED Illuminator

Manufacturer:
Advanced Illumination

Geometry:
Spot Light

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Contains SVHC\(s\)](#)
