


TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy


TECHSPEC® ACHROMATIC LENSES



63691
MON APR 27 2009 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 1.299
CED RADIUS : 2.696
SCALE BAR : 10

REFERENCE : CHIEF RAY


EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



CHROMATIC FOCAL SHIFT

63691
MON APR 27 2009
MAXIMUM FOCAL SHIFT RANGE: 36.1153 μm
DIFFRACTION LIMITED RANGE: 18.005 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

63691
MON APR 27 2009
MAXIMUM SCALE: $\pm 20.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

63691
MON APR 27 2009
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

EO Edmund
optics | worldwide

www.edmundoptics.com