


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: Aluminum w/ Protective Overcoat
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE



3. FINE GRIND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40-20	40-20				
CLEAR APERTURE	25.46 x 18.00	18.00 x 18.00				
COATING APERTURE	25.46 x 18.00	18.00 x 18.00	TITLE 20mm, Aluminum Coated, N-BK7 High Tolerance RA Prism			
SURFACE FLATNESS	λ/8	λ/8				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO 32548	SHEET 1 OF 1