


NOTES:

- 1. SUBSTRATE MATERIAL:
N-BK7
- 2. ROHS COMPLIANT
- 3. SURFACE S1 IS PARALLEL TO SURFACE S2 WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 30% R $\pm 5\%$ @ 550nm
70% T $\pm 5\%$ @ 550nm



S2: AR R(avg) $\leq 1\%$, R(abs) $\leq 2\%$ @ 400 - 700nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO		TITLE	25 x 38mm, 30 R/70 T, PLATE BEAMSPLITTER	
ANGLE OF INCIDENCE	45°	45°		DWG NO	48392	SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm		ALL DIMS IN	mm	