





- NOTES:
- 1. SUBSTRATE: BOROFLOAT®
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: R(AVG) > 90% @ 750 - 1125nm @ 45° AOI
 - T(AVG) > 85% @ 425 - 675nm @ 45° AOI
 - S2: NONE
 - 3. FINE GRIND SURFACE
 - 4. RoHS: COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	20.0 x 20.0mm, 45° AOI, HOT MIRROR	
SURFACE QUALITY	80 - 50	80 - 50		DWG NO	62628	SHEET 1 OF 1
SURFACE FLATNESS	4 - 6λ	4 - 6λ				
MIN CLEAR APERTURE	17.00 x 17.00	17.00 x 17.00				
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		