
NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. ROHS COMPLIANT

- 3. SURFACE \$1 IS PARALLEL TO SURFACE \$2 WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: 60% R ±5% @ 550nm 40% T ±5% @ 550nm
 - S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 700nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2			R	Edmund Optic	CS®
SHAPE	PLANO	PLANO					
ANGLE OF INCIDENCE	45°	45°	THIRD ANGLE _ PROJECTION			25 x 38mm, 40 R/60 T, PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40		$\psi \neg$			0.1557
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN	mm	DWG NO	68407	Sheet 1 Of 1