NOTES:

1. SUBSTRATE MATERIAL: N-BK7


- 2. ROHS COMPLIANT
- 3. SURFACE S1 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)


\$1: 70% R ±5% @ 550nm 30% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm



CUT WITH 0.25mm MAXIMUM EDGE CHIP





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
ANGLE OF INCIDENCE	45°	45°	
SURFACE QUALITY	60-40	60-40	
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	

	80	®	E	dmund Optics®	

			-	
THIRD ANGLE PROJECTION		TITLE	35 x 35mm, 70 R/30 T, PLATE BEAMSPLITTER	
ALL DIMS IN	mm	DWG NO	49757	SHEET 1 OF 1