


NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: NONE  
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	CONCAVE	PLANO				
EFFECTIVE FOCAL LENGTH	152.4mm	N/A				
FOCAL LENGTH TOLERANCE	±2%	N/A				
APERTURE	f/2	N/A				
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

Ø3in, 6in FL PROTECTED GOLD, SPHERICAL MIRROR

DWG NO

32828

SHEET  
1 OF 1