

NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RABS ≤0.25% @ 880nm RAVG ≤1.25% @ 400 - 870nm RAVG ≤1.25% @ 890 - 1000nm



5. Rohs Compliant





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

S1 S2	2
SHAPE PLANO PLA	NO
SURFACE QUALITY 60-40 60-	40
CLEAR APERTURE Ø45.00 Ø45	5.00
PROTECTIVE AS NEEDED PROTECTIVE	AS NEEDED

			Edmund Option	;S®
THIRD ANGLE PROJECTION	$\phi \Box$	TITLE	50mm DIA., 4mm THICK, VIS-NIR COA λ/4 N-BK7 WINDOW	TED
ALL DIMS IN	mm	DWG NO	48447	SHEET