


NOTES:


1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: NONE  
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A		S1	S2	<div>DIMENSIONS ARE FOR REFERENCE ONLY</div> <div><div><div><div></div><div></div></div><div><div></div><div></div></div></div><div><div></div><div></div></div><div>Edmund Optics®</div></div>					
SHAPE		CONCAVE	PLANO						
EFFECTIVE FOCAL LENGTH		304.8mm	N/A						
FOCAL LENGTH TOLERANCE		±2%	N/A						
APERTURE		f/4	N/A						
SURFACE QUALITY		60-40	60-40	<div>THIRD ANGLE PROJECTION</div> 	TITLE		Ø3in, 12in FL UNCOATED, SPHERICAL MIRROR		
SURFACE FLATNESS		λ/4	λ/4		ALL DIMS IN		mm	DWG NO	49599
BEVEL		PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						

**Edmund Optics®**