

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING





FOCAL LENGTH FL (mm)	4	
MAGNIFICATION	50X	
MOUNTING THREAD	M26 x 36 TPI	
NUMERICAL APERTURE NA	0.75	
WORKING DISTANCE (mm)	5.2	
LENGTH EXCLUDING THREADS (mm)	89.8	
MAXIMUM DIAMETER (mm)	34	
TYPE	Microscope Objective	
COMPATIBLE TUBE LENS	Focal Length: 200mm	
DEPTH OF FOCUS (µm)	0.5	
ENTRANCE PUPIL (mm)	10	
FIELD OF VIEW, 1/2" SENSOR	0.13 x 0.10mm	
FIELD OF VIEW, 18 DIAMETER FIELD EYEPIECE (mm)	0.36	
FIELD OF VIEW, 2/3" SENSOR	0.18 x 0.13mm	
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	0.48	
RESOLVING POWER (µm)	0.3	
WAVELENGTH RANGE (nm)	435 - 655	
RoHS	Exempt	

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE TITLE 50X Mitutoy

ALL DIMS IN mm DWG NO 58237

50X Mitutoyo Plan Apo HR Infinity Corrected Objective

58237 SHEET 1 OF 1