


NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: Multi-Layer DiElectric
T(AVG) ≥90% @ 800 - 1200nm
R(AVG) ≥95% @ 425 - 650nm
S2: NONE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

S1		S2		THIRD ANGLE PROJECTION		TITLE	45° Cold Mirror Mounted in C-Mount Cube	
SURFACE QUALITY	80-50		80-50	ALL DIMS IN	mm	DWG NO	62642	SHEET 1 OF 1