





FOCAL LENGTH (EFL): 75 ±0,75  
BACK FOCAL LENGTH (BFL): 71,96

1 AR COATING: NONE

| LEFT SURFACE                                                                       |                          |             | MATERIAL                                                                            | RIGHT SURFACE                                                                                                 |                                             |                 |
|------------------------------------------------------------------------------------|--------------------------|-------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|---------------------------------------------|-----------------|
| R                                                                                  | 34,385±0,034 CX          |             | GLASS FUSED SILICA 458/678                                                          | R                                                                                                             | ∞ PL                                        |                 |
| Øe                                                                                 | 24                       |             |                                                                                     | Øe                                                                                                            | 24                                          |                 |
| 3/                                                                                 | 0,5 (0,1) λ=632,8 nm     |             |                                                                                     | 3/                                                                                                            | 0,5 (0,1) λ=632,8 nm                        |                 |
| 4/                                                                                 | -                        |             |                                                                                     | 4/                                                                                                            | 2,18'                                       |                 |
| 5/                                                                                 | 20 - 10 (MIL-PRF-13830B) |             |                                                                                     | 5/                                                                                                            | 20 - 10 (MIL-PRF-13830B)                    |                 |
| 6/                                                                                 | -                        |             |                                                                                     | 6/                                                                                                            | -                                           |                 |
| PROTECTIVE CHAMFERS AS NEEDED                                                      |                          |             | FIRST ANGLE PROJECTION                                                              | <div> Edmund Optics®</div> |                                             |                 |
| ROHS:<br>COMPLIANT                                                                 | SCALE:<br>NONE           | λ = 587,6nm |                                                                                     |                                                                                                               |                                             |                 |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                          |             |  | TITLE                                                                                                         | 25mm Dia, x 75mm FL Uncoated, λ/20 PCX Lens |                 |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING                     |                          |             |                                                                                     | ALL DIMS IN:                                                                                                  | mm                                          |                 |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                           |                          |             | DWG NO                                                                              | 33052                                                                                                         | SHEET SIZE<br>A4                            | SHEET<br>1 OF 1 |