NOTES:

SHAPE

MIN CLEAR APERTURE


BEVEL MAX FACE

- 1. SUBSTRATE: FUSED SILICA
- 2. BEAM MODE: SM OR MM
- 3. SAMPLED ENERGY: 73
- 4. SAMPLED ANGLE: 4.0 x 4.0
- 5. COATING: LASER V-COAT (1064nm)
- 6. BEAM SPECIFICATION: MINIMUM BEAM DIAMETER: 0.37mm

Ø16.2

PROTECTIVE AS NEEDED PROTECTIVE AS NEEDED

Ø16.2



ALL DIMS IN

mm

DWG NO

14692

SHEET

1 OF 1