



NOTES:
1. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	VALUE
DESIGN WAVELENGTH DWL (nm)	266
INPUT DIAMETER (mm)	12.0 - 12.1mm (1/e ²)
WAVELENGTH RANGE (nm)	250 - 270



ALL DIMS IN mm

TITLE	266nm Flat Top Beam Shaper πShaper 12_12_266_HP		
DWG NO	15498	SHEET	1 OF 1