

## NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) <0.25% @ 532nm R(ABS) <0.25% @ 1064nm R(AVG) <1.0% @ 500 - 1100nm



5. Rohs Compliant







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE (mm)	Ø22.86	Ø22.86
BEVEL F	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION	<b>\$</b>	TITLE
ALL DIMS IN	mm	DWG

Edmund Optics®
25.4mm DIA., 4mm THICK, YAG-BBAR COATED, λ/4 N-BK7 WINDOW

DIMS IN	mm	DWG NO	15793	SHEE 1 OF