

NOTES:


- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE S1 & S2: R(AVG) <0.5% @ 350 - 700nm
- 3. SURFACE S2 TO BE PARALLEL WITH S1 TO <5 ARCSEC



5. Rohs Compliant







FOR INFORMATION ONLY DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 20-10 | 20-10 |
| CLEAR APERTURE | Ø24.00 Ø24.00 | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |
| | | |

| | | G | Edmund Optics® | | |
|--------------|-------------|----------|--|-----------------|--|
| HIRD ANGLE - | $\phi \lhd$ | TITLE | 30mm DIA., 4mm THICK, VIS-EXT COATE FUSED SILICA WINDOW | D, λ/10 | |
| ALL DIMS IN | mm | DWG NO | 16461 | SHEET 1 OF 1 | |