


NOTES:




1. SUBSTRATE:  
HOYA GLASS: ND-0.3
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <0.02 mm

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**




3. FINE GRIND SURFACE

4. COATING SPECIFICATION:  
S1 & S2:R(AVG)  $\leq 0.4\%$  @ 425 - 675nm
5. OPTICAL DENSITY: 3 +/-0.3 @ 400-700nm
6. TRANSMISSION (%): 0.1% AVERAGE FROM 400-700nm
7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE 		TITLE	3.0 OD, 25mm DIA., VIS 0° COATED, ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO			TITLE		
SURFACE QUALITY	80-50	80-50			TITLE		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13109	SHEET 1 OF 1