

1. SUBSTRATE:
SCHOTT NG9





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

5. TRANSMISSION (%): 0.005% AVERAGE FROM 400-700nm


6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	SCHOTT NG9, 4.3 OD, 12.5mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO			DWG NO	16658	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50			ALL DIMS IN	mm	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					