

NOTES:

1. SUBSTRATE:
SCHOTT NG9

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 3.3


5. TRANSMISSION (%): 0.05

- ## 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE			SCHOTT NG9, 3.3 OD, 25mm DIA., ABSORPTIVE ND FILTER		
SHAPE	PLANO	PLANO								
SURFACE QUALITY	80-50	80-50								
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16671			SHEET 1 OF 1	