

NOTES:

1. SUBSTRATE:
SCHOTT NG9

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**


2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE


4. OPTICAL DENSITY: 4.0

5. TRANSMISSION (%): 0.01


6. ROHS COMPLIANT



$\varnothing 25.00_{\pm 0.38}$



— 2.80 NOMINAL



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



Edmund Optics®

TITLE

SCHOTT NG9, 4.0 OD, 25mm DIA.,
ABSORPTIVE ND FILTER

DWG NO

16673

SHEET
1 OF 1

S1

S2

PLANO

PLANO


80-50

80-50

PROTECTIVE AS NEEDED

PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED