





1. SUBSTRATE:
SCHOTT NG11

3. COATING SPECIFICATION:
S1 & S2:NONE


5. TRANSMISSION (%): 63.1% AVERAGE FROM 400-700nm

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	SCHOTT NG11, 0.2 OD, 12.5mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO			TITLE		
SURFACE QUALITY	80-50	80-50			TITLE		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16720	SHEET 1 OF 1