Edmund optics | worldwide

Family ID #1669

TECHSPEC® Precision Optical Flat Mirrors



- Fused Silica and ZERODUR® Substrates
- λ/10 and λ/20 Surface Flatness
- Variety of Coating Options Offered

Common Specifications

General

Note:	Flatness is specified as Peak to Valley

Physical & Mechanical Properties

Back Surface:	Commercial Polish

Optical Properties

Surface Quality:	60-40	**Coating Type:**	Metal

Technical Information

Products

Surface Flatness (P-V)	Dia. (mm)	Substrate	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
λ/10	12.70	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	3.20	#43-319-522	£84.92 Volume Pricing	1 In Stock
λ/20	12.70	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	3.20	#43-400-522	£115.57 Volume Pricing	4 In Stock
λ/10	12.70	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	3.20	#43-327-522	£92.80 Volume Pricing	1 In Stock
λ/20	12.70	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	3.20	#43-404-522	£132.20 Volume Pricing	4 In Stock
λ/10	12.70	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.20	#43-319-533	£89.30 Volume Pricing	5 In Stock
λ/20	12.70	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.20	#43-400-533	£119.94 Volume Pricing	20+ In Stock
λ/10	12.70	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.20	#43-327-533	£97.18 Volume Pricing	1 In Stock
λ/20	12.70	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.20	#43-404-533	£136.58 Volume Pricing	2 In Stock
λ/10	12.70	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.20	#43-319-566	£102.43 Volume Pricing	20+ In Stock
λ/20	12.70	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.20	#43-400-566	£133.08 Volume Pricing	Contact Us
λ/10	12.70	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.20	#43-327-566	£110.31 Volume Pricing	Contact Us

λ/20	12.70	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.20	#43-404-566	£149.71 Volume Pricing	5 In Stock
λ/10	12.70	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.20	#43-319-577	£98.06 Volume Pricing	20+ In Stock
λ/20	12.70	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.20	#43-400-577	£128.70 Volume Pricing	5 In Stock
λ/10	12.70	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.20	#43-327-577	£105.94 Volume Pricing	Contact Us
λ/20	12.70	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.20	#43-404-577	£145.33 Volume Pricing	2 In Stock
λ/10	25.40	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#01-913-522	£125.20 Volume Pricing	5 In Stock
λ/20	25.40	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#43-408-522	£181.23 Volume Pricing	8 In Stock
λ/10	25.40	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#32-195-522	£140.96 Volume Pricing	3 In Stock
λ/20	25.40	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#43-412-522	£188.23 Volume Pricing	Contact Us
λ/10	25.40	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#01-913-533	£129.57 Volume Pricing	3 In Stock
λ/20	25.40	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#43-408-533	£185.61 Volume Pricing	20+ In Stock
λ/10	25.40	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#32-195-533	£145.33 Volume Pricing	2 In Stock

λ/20	25.40	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#43-412-533	£192.61 Volume Pricing	1 In Stock
λ/10	25.40	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#01-913-566	£147.08 Volume Pricing	Contact Us
λ/20	25.40	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#43-408-566	£203.12 Volume Pricing	1 In Stock
λ/10	25.40	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#32-195-566	£162.84 Volume Pricing	6 In Stock
λ/20	25.40	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#43-412-566	£210.12 Volume Pricing	6 In Stock
λ/10	25.40	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#01-913-577	£164.59 Volume Pricing	4 In Stock
λ/20	25.40	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#43-408-577	£220.63 Volume Pricing	Contact Us
λ/10	25.40	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#32-195-577	£180.35 Volume Pricing	6 In Stock
λ/20	25.40	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#43-412-577	£227.63 Volume Pricing	4 In Stock
λ/10	50.80	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#01-914-522	£209.24 Volume Pricing	4 In Stock
λ/20	50.80	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#43-416-522	£273.16 Volume Pricing	6 In Stock

λ/10	50.80	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#32-199-522	£231.13 Volume Pricing	Contact Us
λ/20	50.80	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	12.70	#43-420-522	£315.18 Volume Pricing	4 In Stock
λ/10	50.80	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#01-914-533	£231.13 Volume Pricing	4 In Stock
λ/20	50.80	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#43-416-533	£295.04 Volume Pricing	Contact Us
λ/10	50.80	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#32-199-533	£253.02 Volume Pricing	1 In Stock
λ/20	50.80	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	12.70	#43-420-533	£337.07 Volume Pricing	6 In Stock
λ/10	50.80	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#01-914-566	£283.66 Volume Pricing	4 In Stock
λ/20	50.80	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#43-416-566	£347.57 Volume Pricing	10 In Stock
λ/10	50.80	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#32-199-566	£305.55 Volume Pricing	1 In Stock
λ/20	50.80	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	12.70	#43-420-566	£389.60 Volume Pricing	3 In Stock
λ/10	50.80	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#01-914-577	£274.91 Volume Pricing	Contact Us
λ/20	50.80	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#43-416-577	£338.82 Volume Pricing	3 In Stock

λ/10	50.80	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#32-199-577	£296.79 Volume Pricing	2 In Stock
λ/20	50.80	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.70	#43-420-577	£380.84 Volume Pricing	9 In Stock
λ/10	76.20	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#01-915-522	£446.51 Volume Pricing	Contact Us
λ/20	76.20	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#47-573-522	£503.41 Volume Pricing	5 In Stock
λ/10	76.20	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#31-391-522	£555.94 Volume Pricing	1 In Stock
λ/20	76.20	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#48-117-522	£766.06 Volume Pricing	1 In Stock
λ/10	76.20	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#01-915-533	£490.28 Volume Pricing	2 In Stock
λ/20	76.20	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#47-573-533	£547.19 Volume Pricing	3 In Stock
λ/10	76.20	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#31-391-533	£599.72 Volume Pricing	1 In Stock
λ/20	76.20	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#48-117-533	£809.84 Volume Pricing	2 In Stock
λ/10	76.20	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#01-915-566	£516.55 Volume Pricing	Contact Us
λ/20	76.20	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#47-573-566	£573.45 Volume Pricing	Contact Us

λ/10	76.20	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#31-391-566	£625.98 Volume Pricing	4 In Stock
λ/20	76.20	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#48-117-566	£836.10 Volume Pricing	4 In Stock
λ/10	76.20	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#01-915-577	£507.79 Volume Pricing	Contact Us
λ/20	76.20	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#47-573-577	£564.70 Volume Pricing	5 In Stock
λ/10	76.20	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#31-391-577	£617.23 Volume Pricing	1 In Stock
λ/20	76.20	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#48-117-577	£827.35 Volume Pricing	10 In Stock
λ/10	101.60	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#01-611-522	£801.08 Volume Pricing	1 In Stock
λ/20	101.60	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#47-574-522	£866.75 Volume Pricing	8 In Stock
λ/10	101.60	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#31-392-522	£822.97 Volume Pricing	Contact Us
λ/20	101.60	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	19.10	#48-118-522	£914.90 Volume Pricing	5 In Stock
λ/10	101.60	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#01-611-533	£844.86 Volume Pricing	5 In Stock
λ/20	101.60	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#47-574-533	£910.52 Volume Pricing	2 In Stock

λ/10	101.60	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#31-392-533	£866.75 Volume Pricing	1 In Stock
λ/20	101.60	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	19.10	#48-118-533	£958.67 Volume Pricing	1 In Stock
λ/10	101.60	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#01-611-566	£879.88 Volume Pricing	5 In Stock
λ/20	101.60	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#47-574-566	£945.54 Volume Pricing	3 In Stock
λ/10	101.60	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#31-392-566	£901.77 Volume Pricing	4 In Stock
λ/20	101.60	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	19.10	#48-118-566	£993.69 Volume Pricing	20+ In Stock
λ/10	101.60	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#01-611-577	£866.75 Volume Pricing	4 In Stock
λ/20	101.60	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#47-574-577	£932.41 Volume Pricing	4 In Stock
λ/10	101.60	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#31-392-577	£888.63 Volume Pricing	2 In Stock
λ/20	101.60	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	19.10	#48-118-577	£980.56 Volume Pricing	Contact Us

					#71-130-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!			
λ/10	127.00	Fused Silica (Corning 7980)	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40		£1,343.89 Volume Pricing	1 In Stock
					#71-247-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!			
λ/20	355.60	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	88.90		£12,388.33	Contact Us

						#71-130-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	127.00	Fused Silica (Corning 7980)	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40		£1,418.31 Volume Pricing	1 In Stock
						#71-130-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	127.00	Fused Silica (Corning 7980)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40		£1,466.46 Volume Pricing	1 In Stock

						#71-130-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	127.00	Fused Silica (Corning 7980)	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40		£1,444.58 Volume Pricing	1 In Stock
						#71-131-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	127.00	Fused Silica (Corning 7980)	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40		£1,781.64 Volume Pricing	1 In Stock
						#71-131-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	127.00	Fused Silica (Corning 7980)	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40		£1,856.06 Volume Pricing	1 In Stock

						#71-247-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	355.60	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	88.90		£12,432.10	Contact Us
						#71-131-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	127.00	Fused Silica (Corning 7980)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40		£1,904.21 Volume Pricing	1 In Stock
						#71-247-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	355.60	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	88.90		£13,132.50	Contact Us

						#71-131-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£1,882.33 Volume Pricing	Contact Us
λ/20	127.00	Fused Silica (Corning 7980)	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40			
						#71-247-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£12,869.85	Contact Us
λ/20	355.60	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	88.90			
λ/10	152.40	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40	#01-612-522	£1,746.62 Volume Pricing	2 In Stock
λ/20	152.40	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40	#47-575-522	£2,473.29 Volume Pricing	4 In Stock
λ/10	152.40	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40	#31-393-522	£1,869.19 Volume Pricing	2 In Stock
λ/20	152.40	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	25.40	#48-119-522	£2,775.34 Volume Pricing	2 In Stock

λ/10	152.40	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40	#01-612-533	£1,790.40 Volume Pricing	6 In Stock
λ/20	152.40	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40	#47-575-533	£2,517.06 Volume Pricing	5 In Stock
λ/10	152.40	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40	#31-393-533	£1,912.97 Volume Pricing	Contact Us
λ/20	152.40	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	25.40	#48-119-533	£2,819.11 Volume Pricing	2 In Stock
λ/10	152.40	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40	#01-612-566	£1,899.84 Volume Pricing	5 In Stock
λ/20	152.40	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40	#47-575-566	£2,626.50 Volume Pricing	3 In Stock
λ/10	152.40	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40	#31-393-566	£2,022.41 Volume Pricing	1 In Stock
λ/20	152.40	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	25.40	#48-119-566	£2,928.55 Volume Pricing	2 In Stock
λ/10	152.40	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40	#01-612-577	£1,877.95 Volume Pricing	1 In Stock
λ/20	152.40	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40	#47-575-577	£2,604.61 Volume Pricing	Contact Us
λ/10	152.40	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40	#31-393-577	£2,000.52 Volume Pricing	4 In Stock

λ/20	152.40	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	25.40	#48-119-577	£2,906.66 Volume Pricing	3 In Stock
λ/10	203.20	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#31-390-522	£3,567.66 Volume Pricing	2 In Stock
λ/20	203.20	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#49-048-522	£4,390.63 Volume Pricing	Contact Us
λ/10	203.20	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#31-394-522	£3,777.78 Volume Pricing	1 In Stock
λ/20	203.20	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#49-049-522	£4,517.58 Volume Pricing	Contact Us
λ/10	203.20	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#31-390-533	£3,633.33 Volume Pricing	4 In Stock
λ/20	203.20	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#49-048-533	£4,456.30 Volume Pricing	1 In Stock
λ/10	203.20	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#31-394-533	£3,843.45 Volume Pricing	1 In Stock
λ/20	203.20	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#49-049-533	£4,583.24 Volume Pricing	5 In Stock
λ/10	203.20	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#31-390-566	£3,742.76 Volume Pricing	1 In Stock
λ/20	203.20	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#49-048-566	£4,565.73 Volume Pricing	4 In Stock
λ/10	203.20	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#31-394-566	£3,952.88 Volume Pricing	2 In Stock

λ/20	203.20	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#49-049-566	£4,692.68 Volume Pricing	5 In Stock
λ/10	203.20	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#31-390-577	£3,720.88 Volume Pricing	2 In Stock
λ/20	203.20	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#49-048-577	£4,543.85 Volume Pricing	Contact Us
λ/10	203.20	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#31-394-577	£3,931.00 Volume Pricing	1 In Stock
λ/20	203.20	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#49-049-577	£4,670.79 Volume Pricing	Contact Us
λ/10	254.00	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#46-715-522	£5,428.10 Volume Pricing	1 In Stock
λ/20	254.00	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#65-879-522	£7,993.32 Volume Pricing	Contact Us
λ/10	254.00	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#46-715-533	£5,515.65 Volume Pricing	4 In Stock
λ/20	254.00	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#65-879-533	£8,080.87 Volume Pricing	Contact Us
λ/10	254.00	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#46-715-566	£5,625.09 Volume Pricing	1 In Stock
λ/20	254.00	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#65-879-566	£8,190.30 Volume Pricing	2 In Stock

λ/10	254.00	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#46-715-577	£5,603.20 Volume Pricing	3 In Stock
λ/20	254.00	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#65-879-577	£8,168.42 Volume Pricing	4 In Stock
λ/10	254.00	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#71-108-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£5,471.88 Volume Pricing	Contact Us
λ/20	254.00	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#71-110-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£7,923.28 Volume Pricing	Contact Us

						#71-108-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	254.00	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10		£5,559.43 Volume Pricing	Contact Us
						#71-110-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	254.00	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10		£8,010.83 Volume Pricing	Contact Us

						#71-108-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	254.00	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10		£5,668.86 Volume Pricing	Contact Us
						#71-110-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	254.00	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10		£8,120.26 Volume Pricing	Contact Us

						#71-108-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	254.00	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10		£5,646.98 Volume Pricing	Contact Us
						#71-110-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	254.00	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10		£8,098.38 Volume Pricing	Contact Us
λ/10	304.80	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#69-921-522	£7,078.42 Volume Pricing	Contact Us
λ/20	304.80	Fused Silica	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#65-880-522	£10,816.80 Volume Pricing	Contact Us

λ/10	304.80	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#71-109-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£7,113.44 Volume Pricing	Contact Us
λ/20	304.80	ZERODUR®	R_{avg} >85% @ 400 - 700nm R_{avg} >90% @ 400 - 2000nm	Protected Aluminum (400-2000nm)	38.10	#71-111-522 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£10,834.31 Volume Pricing	Contact Us
λ/10	304.80	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#69-921-533	£7,144.08 Volume Pricing	1 In Stock

						#71-109-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£7,179.10 Volume Pricing	Contact Us
λ/10	304.80	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10			
						#71-111-533 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£10,899.98 Volume Pricing	Contact Us
λ/20	304.80	ZERODUR®	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10			
λ/20	304.80	Fused Silica	R_{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	38.10	#65-880-533	£10,882.47 Volume Pricing	Contact Us
λ/10	304.80	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#69-921-566	£7,253.52 Volume Pricing	1 In Stock

						#71-109-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	304.80	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10		£7,288.54 Volume Pricing	Contact Us
						#71-111-566 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	304.80	ZERODUR®	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10		£11,009.41 Volume Pricing	Contact Us
λ/20	304.80	Fused Silica	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	38.10	#65-880-566	£10,991.90 Volume Pricing	Contact Us
λ/10	304.80	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#69-921-577	£7,231.63 Volume Pricing	1 In Stock
λ/20	304.80	Fused Silica	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10	#65-880-577	£10,970.02 Volume Pricing	Contact Us

						#71-109-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/10	304.80	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10		£7,266.65 Volume Pricing	Contact Us
						#71-111-577 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
λ/20	304.80	ZERODUR®	R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	38.10		£10,987.53 Volume Pricing	Contact Us

Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com