

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Commercial Grade Standard Microscope Objectives



- Achromatic and Plan Designs
- Use with T- and C-Mounting Systems
- Ideal for OEM Applications

Common Specifications

Physical & Mechanical Properties

Maximum Diameter (mm):	24
------------------------	----

Threading & Mounting

Mounting Threads:	0.7965-36 TPI, 55° Whitworth
-------------------	------------------------------

Environmental & Durability Factors

Operating Temperature (°C):	5 to 40	Storage Temperature (°C):	-20 to 60
Operating Relative Humidity:	45% to 85%		

Technical Information

Products

Magnification	NA	Type	WD (mm)	Stock Number	Price	Buy
4X	0.10	Plan	15.25	#67-706	£108.80	10 In Stock
4X	0.10	Achromatic	18.8	#43-902	£77.35	20+ In Stock
10X	0.25	Plan	1.5	#43-907	£135.15	14 In Stock
10X	0.25	Achromatic	6.14	#43-903	£90.10	20+ In Stock
40X	0.65	Achromatic, Spring-Loaded	0.48	#43-904	£117.30	20+ In Stock
100X	1.25	Plan, Spring- Loaded	0.1	#43-909	£292.40	7 In Stock
100X	1.25	Achromatic, Spring-Loaded	0.1	#43-905	£148.75	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com