

[All Products](#) / [Test Targets](#) / [Color & Gray Level Test Targets](#)

Spectralon® White Balance and Diffuse Reflectance Targets



- Diffuse Reflectance with 99% Nominal Reflectance in UV-VIS-NIR Wavelength Range (350 - 1600nm)
- Durable, Stable, and Washable
- NIST Traceable Calibration Certificate and Data from 250 - 2500nm

Common Specifications

General

NIST Certification: Yes

Optical Properties

Nominal Reflectance (%): 99

Threading & Mounting

Mounting: Rugged Anodized Aluminum

Material Properties

Reflective Material: Spectralon®

Environmental & Durability Factors

Operating Temperature (°C): -80 to 350

Operating Relative Humidity: 5% - 95%

Technical Information

Products

Title	Stock Number	Price	Buy
2" Spectralon® White Balance and Diffuse Reflectance Targets	#58-609	£956.00 Volume Pricing	10 In Stock
5" Spectralon® White Balance and Diffuse Reflectance Targets	#58-610	£1,196.00 Volume Pricing	2 In Stock
10" Spectralon® White Balance and Diffuse Reflectance Targets	#58-611	£2,236.00 Volume Pricing	5 In Stock
12" Spectralon® White Balance and Diffuse Reflectance Targets	#58-612	£2,636.00 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com