

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

TECHSPEC® HEO Series M12 Lenses



- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length

Common Specifications

General			
Series:	HEO Series	IR Cut Filter:	No
Imaging Lens Type:	Meets IEC IPX7 and IPX9K		
Physical & Mechanical Properties			
Iris Option:	Fixed		
Weight (g):	4		
Optical Properties			
Working Distance (mm):		400 - ∞	
Sensor			
Pixel Size (µm):	5.00		
Threading & Mounting			
Filter Thread:	N/A		
Mount:	S-Mount (M12 x 0.5)		
Environmental & Durability Factors			
Environmental Rating:		IPX7 and IPX9K	
Type of Ruggedization:		Waterproof (IPX7 and IPX9K)	

Technical Information

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	Wavelength	Stock Number	Price	Buy
2.20	f/2	1/3"	400 - ∞	VIS	#58-840	£128.00 Volume Pricing	20+ In Stock
3.60	f/2.5	1/3"	400 - ∞	VIS	#58-841	£128.00 Volume Pricing	15 In Stock
8.00	f/2.5	1/1.7"	400 - ∞	VIS	#63-759	£128.00 Volume Pricing	Contact Us
2.20	f/2	1/3"	400 - ∞	NIR	#58-844	£128.00 Volume Pricing	Contact Us
3.60	f/2.5	1/3"	400 - ∞	NIR	#58-845	£128.00 Volume Pricing	Contact Us
8.00	f/2.5	1/2"	400 - ∞	NIR	#63-761	£128.00 Volume Pricing	3 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com