

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC® $\lambda/10$ First Surface Mirrors



- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground

Optical Properties

Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	20-10
--------------------------------	--------------	-------------------------	-------

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Thickness (mm)	Coating	Coating Specification	Stock Number	Price	Buy
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450- 650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-007	£69.61 Volume Pricing	1 In Stock
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250- 700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-307	£69.61 Volume Pricing	5 In Stock
5.00	$\lambda/10$	-	2.00	Protected Gold (700- 10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-021	£86.67 Volume Pricing	Contact Us
5.00	$\lambda/10$	-	2.00	Protected Silver (450- 10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-321	£83.17 Volume Pricing	20+ In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (600- 1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-976	£85.37 Volume Pricing	14 In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (800- 1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-006	£85.37 Volume Pricing	7 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (450- 650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-008	£69.61 Volume Pricing	20+ In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (250- 700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-308	£69.61 Volume Pricing	3 In Stock

-	$\lambda/10$	5.0 x 5.0	2.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-022	£86.67 Volume Pricing	1 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-322	£83.17 Volume Pricing	1 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-977	£85.37 Volume Pricing	8 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-007	£85.37 Volume Pricing	2 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-189	£69.61 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-188	£69.61 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-186	£86.67 Volume Pricing	Contact Us
6.35	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-187	£83.17 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-009	£69.61 Volume Pricing	20+ In Stock

10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-309	£69.61 Volume Pricing	5 In Stock
10.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-023	£86.67 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-323	£83.17 Volume Pricing	20+ In Stock
10.00	$\lambda/10$	-	2.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-233	£86.67 Volume Pricing	17 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-979	£85.37 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-009	£85.37 Volume Pricing	3 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-010	£69.61 Volume Pricing	20+ In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-310	£69.61 Volume Pricing	14 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-024	£86.67 Volume Pricing	15 In Stock

-	$\lambda/10$	10.0 x 10.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-324	£83.17 Volume Pricing	17 In Stock
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-409	£69.61 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-419	£69.61 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-429	£86.67 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-439	£83.17 Volume Pricing	15 In Stock
12.50	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-234	£86.67 Volume Pricing	5 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-980	£85.37 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-010	£85.37 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-410	£69.61 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-420	£69.61 Volume Pricing	Contact Us

-	$\lambda/10$	12.5 x 12.5	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-430	£86.67 Volume Pricing	13 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-440	£83.17 Volume Pricing	8 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-196	£69.61 Volume Pricing	Contact Us
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-195	£69.61 Volume Pricing	Contact Us
12.70	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-193	£86.67 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-194	£83.17 Volume Pricing	11 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-011	£74.85 Volume Pricing	7 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-311	£74.85 Volume Pricing	4 In Stock
15.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-025	£91.93 Volume Pricing	2 In Stock
15.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-325	£89.74 Volume Pricing	20+ In Stock
15.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-235	£100.68 Volume Pricing	1 In Stock

15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-982	£91.93 Volume Pricing	5 In Stock
15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-012	£91.93 Volume Pricing	7 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-012	£74.85 Volume Pricing	5 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-312	£80.99 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-026	£91.93 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-326	£89.74 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-997	£91.93 Volume Pricing	6 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-203	£80.99 Volume Pricing	7 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-202	£80.99 Volume Pricing	3 In Stock

19.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-200	£100.68 Volume Pricing	1 In Stock
19.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-201	£94.12 Volume Pricing	3 In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-013	£80.99 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-313	£80.99 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-027	£100.68 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-327	£94.12 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-236	£100.68 Volume Pricing	7 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-984	£98.50 Volume Pricing	10 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-014	£98.50 Volume Pricing	2 In Stock

-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-014	£80.99 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-314	£80.99 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-028	£100.68 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-328	£94.12 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-998	£98.50 Volume Pricing	3 In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-015	£85.37 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-315	£85.37 Volume Pricing	8 In Stock
25.00	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-029	£118.19 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-329	£109.44 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-237	£112.94 Volume Pricing	5 In Stock

25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-985	£112.94 Volume Pricing	12 In Stock
25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-015	£112.94 Volume Pricing	14 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-016	£85.37 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-316	£85.37 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-030	£118.19 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-330	£109.44 Volume Pricing	16 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#25-549	£144.46 Volume Pricing	9 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-999	£112.94 Volume Pricing	4 In Stock
25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-210	£85.37 Volume Pricing	8 In Stock

25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-209	£85.37 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-207	£118.19 Volume Pricing	14 In Stock
25.40	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-208	£109.44 Volume Pricing	20+ In Stock
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-411	£109.44 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-421	£109.44 Volume Pricing	5 In Stock
30.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-431	£148.84 Volume Pricing	14 In Stock
30.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-441	£118.19 Volume Pricing	6 In Stock
30.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-238	£126.95 Volume Pricing	13 In Stock
30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-987	£126.95 Volume Pricing	3 In Stock

30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-017	£126.95 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-412	£109.44 Volume Pricing	20+ In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-422	£109.44 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-432	£148.84 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-442	£118.19 Volume Pricing	4 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-000	£126.95 Volume Pricing	1 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-413	£122.57 Volume Pricing	20+ In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-423	£122.57 Volume Pricing	6 In Stock
35.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-433	£157.59 Volume Pricing	Contact Us

35.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-443	£144.46 Volume Pricing	20+ In Stock
35.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-239	£153.21 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-988	£148.84 Volume Pricing	7 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#25-546	£122.57 Volume Pricing	4 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#25-547	£122.57 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#25-548	£157.59 Volume Pricing	14 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-031	£148.84 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-018	£148.84 Volume Pricing	4 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-414	£122.57 Volume Pricing	14 In Stock

-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-424	£122.57 Volume Pricing	9 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-434	£157.59 Volume Pricing	1 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-444	£144.46 Volume Pricing	20+ In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-001	£148.84 Volume Pricing	4 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-217	£131.33 Volume Pricing	3 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-216	£131.33 Volume Pricing	20+ In Stock
38.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-214	£174.22 Volume Pricing	1 In Stock
38.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-215	£161.97 Volume Pricing	5 In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-017	£131.33 Volume Pricing	Contact Us
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-317	£131.33 Volume Pricing	5 In Stock

40.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-031	£174.22 Volume Pricing	16 In Stock
40.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-331	£161.97 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-240	£175.10 Volume Pricing	12 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-990	£166.35 Volume Pricing	5 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-020	£166.35 Volume Pricing	3 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-018	£131.33 Volume Pricing	10 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-318	£131.33 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-032	£174.22 Volume Pricing	11 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-332	£161.97 Volume Pricing	20+ In Stock

50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-019	£144.46 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-319	£144.46 Volume Pricing	Contact Us
50.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-033	£192.61 Volume Pricing	2 In Stock
50.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-333	£179.48 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-241	£205.74 Volume Pricing	14 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-991	£183.86 Volume Pricing	8 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-021	£183.86 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-020	£144.46 Volume Pricing	9 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-320	£144.46 Volume Pricing	20+ In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-034	£192.61 Volume Pricing	6 In Stock

-	$\lambda/10$	50.0 x 50.0	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-334	£179.48 Volume Pricing	10 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-224	£144.46 Volume Pricing	5 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-223	£144.46 Volume Pricing	7 In Stock
50.80	$\lambda/10$	-	9.53	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-221	£192.61 Volume Pricing	3 In Stock
50.80	$\lambda/10$	-	9.53	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-222	£179.48 Volume Pricing	4 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-415	£297.67 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-425	£297.67 Volume Pricing	5 In Stock
75.00	$\lambda/10$	-	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-435	£385.22 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-445	£358.96 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-416	£297.67 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-426	£297.67 Volume Pricing	7 In Stock

-	$\lambda/10$	75.0 x 75.0	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-436	£385.22 Volume Pricing	2 In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-446	£358.96 Volume Pricing	12 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-417	£436.87 Volume Pricing	12 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-427	£436.87 Volume Pricing	13 In Stock
100.00	$\lambda/10$	-	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-437	£630.36 Volume Pricing	20+ In Stock
100.00	$\lambda/10$	-	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-447	£569.08 Volume Pricing	6 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-418	£436.87 Volume Pricing	10 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-428	£436.87 Volume Pricing	5 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-438	£630.36 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-448	£569.08 Volume Pricing	20+ In Stock
5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#26-094	£69.61 Volume Pricing	Contact Us

5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-098	£69.61 Volume Pricing	2 In Stock
5.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-099	£86.67 Volume Pricing	3 In Stock
5.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-100	£83.17 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-101	£69.61 Volume Pricing	1 In Stock
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-102	£69.61 Volume Pricing	5 In Stock
10.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-103	£86.67 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-104	£83.17 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-105	£69.61 Volume Pricing	1 In Stock
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-364	£69.61 Volume Pricing	4 In Stock
12.50	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-365	£86.67 Volume Pricing	13 In Stock
12.50	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-366	£83.17 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-367	£74.85 Volume Pricing	5 In Stock

15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-368	£74.85 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-369	£91.93 Volume Pricing	3 In Stock
15.00	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-370	£89.74 Volume Pricing	Contact Us
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-371	£80.99 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-372	£80.99 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-373	£100.68 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-374	£94.12 Volume Pricing	3 In Stock
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-375	£85.37 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-376	£85.37 Volume Pricing	5 In Stock
25.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-377	£118.19 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-378	£109.44 Volume Pricing	2 In Stock
30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-379	£109.44 Volume Pricing	1 In Stock

30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#26-380	£109.44 Volume Pricing	4 In Stock
30.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#26-381	£148.84 Volume Pricing	3 In Stock
30.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#26-382	£118.19 Volume Pricing	5 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-924	£744.18 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-925	£744.18 Volume Pricing	2 In Stock
125.00	$\lambda/10$	-	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-926	£853.61 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-927	£809.84 Volume Pricing	2 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-928	£744.18 Volume Pricing	Contact Us
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-929	£744.18 Volume Pricing	1 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-930	£853.61 Volume Pricing	4 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-931	£809.84 Volume Pricing	4 In Stock

150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-932	£1,138.15 Volume Pricing	2 In Stock
150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-933	£1,138.15 Volume Pricing	3 In Stock
150.00	$\lambda/10$	-	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-934	£1,313.25 Volume Pricing	3 In Stock
150.00	$\lambda/10$	-	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-935	£1,225.70 Volume Pricing	Contact Us
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-936	£1,138.15 Volume Pricing	3 In Stock
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-937	£1,138.15 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-938	£1,313.25 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-939	£1,225.70 Volume Pricing	2 In Stock

