

[All Products](#) / [Imaging Lenses](#) / [Telecentric Lenses](#)

High Resolution In-Line Illumination C-Mount Telecentric Lenses



- Designed for High Resolution Imaging
- In-line Illumination Port (0.312" Ferrule)
- 2/3" Max. Sensor Format

Common Specifications

General

Series:	High Res In-Line Illumination C-Mnt Telecentric Lenses	Note:	Magnification Tolerance %: ± 3
Compatible Light Guide/Source:	1/4" (0.312")	Type of Illumination:	In-Line Illumination

Optical Properties

Maximum Image Circle (mm):	11.00
-----------------------------------	-------

Sensor

Maximum Sensor Format:	2/3"
Pixel Size (μm):	2.60

Threading & Mounting

Filter Thread:	N/A
Mount:	C-Mount

Technical Information

Products

Magnification	Max. Sensor Format	Aperture (f/#)	WD (mm)	Type of Illumination	Stock Number	Price	Buy
0.19	2/3"	f/6	110.00	In-Line Illumination	#65-026	£3,687.00	Contact Us
1.00	2/3"	f/7 - Closed	120.00	In-Line Illumination	#65-027	£2,650.00	1 In Stock
2.00	2/3"	f/8 - Closed	100.00	In-Line Illumination	#65-028	£3,028.00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com