

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination High Intensity LED Spot Lights See More

by [Advanced Illumination](#)



- 65mm Coverage at 300mm Working Distance
- M6 Thread for Mounting
- Variable Intensity and Strobed Options

Common Specifications

General

LED Lifetime (hours):	50,000	Type of Illumination:	LED Illuminator
Note:	Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Manufacturer:	Advanced Illumination
Geometry:	Spot Light		

Physical & Mechanical Properties

Height (mm):	26.0		
Dimensions (mm):	66.7 L x 62.0 W	Weight (g):	122.5
Field Coverage (mm):	65.00		

Optical Properties

Working Distance (inches):	6 - 24
-----------------------------------	--------

Electrical

Maximum Trigger Frequency (Hz):	30.00
---------------------------------	-------

Hardware & Interface Connectivity

Connector:	Flying Leads
------------	--------------

Operating Voltage (V):	24.00
------------------------	-------

Power Supply:

Power Supply Required
and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Power Requirement:	90 - 264 V AC @ 47 - 63 Hz
--------------------	-------------------------------

Length of Cable (m):	1.5
----------------------	-----

Threading & Mounting

Mounting Threads:	M4 Nut Channel for Mounting
-------------------	-----------------------------

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
66.7 L x 62.0 W	White	-	#86-429	£486.20	2 In Stock
66.7 L x 62.0 W	Blue	470.00	#86-430	£486.20	Contact Us
66.7 L x 62.0 W	Green	530.00	#86-431	£486.20	Contact Us
66.7 L x 62.0 W	Red	625.00	#86-432	£486.20	1 In Stock
66.7 L x 62.0 W	White	-	#86-433	£663.85	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com