

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus Plan Achromatic Objectives See More by [Olympus](#)



- Ideal for Brightfield, Darkfield, or Fluorescence Microscopy
- Excellent Price-to-Performance Ratio
- Suitable for Introductory and Advanced Optical Microscopy Applications
- Additional [Olympus Infinity Corrected Objectives](#) Available

Common Specifications

General

Compatible Tube Lens
Focal Length (mm):

Focal Length: 180mm

Manufacturer:

Olympus

Physical & Mechanical Properties

Maximum Diameter (mm):

24

Optical Properties

Field Number (mm):

22

Parfocal Length (mm):



45

Threading & Mounting



Mounting Threads:

RMS / 20.32mm x 36 TPI


Technical Information



886-816



Using Olympus Objectives with C-Mount Cameras



Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
2X	0.06	22	90.00	1- U2B221	5.8	#16-879	£672.00	2 In Stock
4X	0.10	22	45.00	1- U2B222	18.5	#86-812	£132.00	11 In Stock
10X	0.25	22	18.00	1- U2B223	10.6	#86-813	£331.20	20+ In Stock
20X	0.40	22	9.00	1- U2B225	1.2	#86-814	£408.00	5 In Stock
40X	0.65	22	4.50	1- U2B227	0.6	#86-815	£604.00	1 In Stock
100X	1.25	22	1.80	1- U2B235	0.15	#86-816	£1,136.00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com