

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Infrared \(IR\) and Ultraviolet \(UV\) Viewers](#)

ZAP-IT® Laser Alignment Paper



- Industrial Standard Beam Profile Viewing Paper
- Records Beam Shape, Divergence, Mode, and Intensity Profile of Pulsed Lasers
- Suitable for Broadband Sources from UV to IR

Common Specifications

General

Note:

Recommended Pulsed Width: 1ns to 30ms

Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Physical & Mechanical Properties

Thickness (inches):	0.009
---------------------	-------

Thickness (mm):	0.24
-----------------	------

Technical Information

Products

Title	Stock Number	Price	Buy
ZAP-IT® Laser Alignment Paper, 2 x 5", Box of 20 Sheets	#15-825	£50.40 Volume Pricing	20+ In Stock
ZAP-IT® Laser Alignment Paper, 2 x 5", Box of 50 Sheets	#15-826	£104.80 Volume Pricing	5 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 20 Sheets	#15-824	£91.20 Volume Pricing	5 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 50 Sheets	#90-709	£160.80 Volume Pricing	16 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", 2mm Sq. Grid Pattern, Box of 20 Sheets	#15-827	£104.80 Volume Pricing	3 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", 2mm Sq. Grid Pattern, Box of 50 Sheets	#15-828	£170.40 Volume Pricing	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com