

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Shutters](#)

C and T-Mount Motorized Shutters

- Male and Female C- and T-Threads for Easy Integration
- Simple On/Off Operation with TTL Input
- M6 and 1/4-20 Tapped Holes for Post Mounting



Common Specifications

General

Deactivation time (ms): 50

Function: Shutter

Electrical

Coil Resistance (Ω): 90 @ 25°C

Coil Resistance Tolerance (%): ± 10

Hardware & Interface Connectivity

Operating Voltage (V): 4.5 V ~ 5.5 V DC

Threading & Mounting

Compatible Post: M6 x 1.0, 1/4-20

Technical Information

Products

Function	Aperture (mm)	Mount	Stock Number	Price	Buy
Shutter	30.0	T-Mount	#11-153	£678.51 Volume Pricing	9 In Stock
Shutter	20.0	C-Mount	#87-208	£512.17 Volume Pricing	10 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com